



2873



Rotary dimmer LV with soft-lock house electronics

Technical Features

Voltage

Operating voltage 230 - 230 V

Frequency

Frequency 50 - 50 Hz

Electric current

Control current 100 - 100 mA

Materials

Material Metal
Plastic

Dimensions

Diameter axis 4 mm
Height 82 mm
Width 82 mm
Depth 67 mm

Architecture

Control/operation element Push & rotative switch

Lighting

Dimmable 230 V LED lamp 3 - 100 W

Texts

Dimming principle Phase cut-on
Fuse Short-circuit and overload-proof (fine-wire fuse)
With spare fuse
Voltage Voltage test possible without dismantling
Installation mode With spreader claws
Type of connection With plug-in terminals
Operation and control No Bluetooth interface
Terminal With terminal for base load from mains isolator

Sustainability

REACH-SVHC free Yes
RoHS conform Yes