



20447109



Thermostat, NO contact, centre plate, time-controlled, K.1, p. white glossy

**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Settings**

Comfort temperature setpoint 10 - 40 °C

**Dimensions**

Height 71 mm

Width 71 mm

Depth 42 mm

**Power supply**

Supply voltage 230 V AC

**Voltage**

Nominal voltage 230 - 230 V

**Electric current**

Max. switching current 10 A

**Materials**

Colour Polar white

**Power**

Standby power consumption (solstandby) 1.20 W

**Use conditions**

Energy efficiency class IV (2%)

**Sustainability**

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes