



HIC410A

Motorized changeover switch 4P 100A 400V

Technical Features

Voltage

Rated operational voltage U_e 380 - 415 V

Electric current

Rated current 100 A

Rated conditional short-circuit current I_{cc} with gl-gG fuses 50 kA

Power

Rated operational power under 400 V AC AC1 65000 W

Architecture

Number of poles 4

Device construction type Fixed built-in

Compatibility

Suitable for DIN Rail Yes

Suitable for distribution board Yes

Installation, mounting

Mounting on DIN rail
Mounting plate

Sustainability

REACH-SVHC free Yes

RoHS conform Yes