



JK116EA3

125A 16 Module DIN Rail Box Plain Door Amendment 3

Technical Features

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of rows	1
With lock	Yes
Has neutral terminal block	Yes

Capacity

Number of modules	16
-------------------	----

Dimensions

Height	300 mm
Width	465 mm
Depth	165.50 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Number of width units	16
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Steel
RAL code	7035
Colour	Light grey

Equipment

Has earthing terminal block	Yes
-----------------------------	-----

Safety

Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Key lock Quarter turn lock

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes