



29531404



LED signal light, white lighting, B.7, al., matt, lacq.

Technical Features

Voltage

Rated voltage 230 V

Power

Power absorbed 1 W

Frequency

Frequency 50 - 60 Hz

Lighting

Type of lamp LED

Materials

Colour Aluminium

RAL code 9006

Surface finish Matt

Material Metal
Plastic

Treatment Varnished

Dimensions

Height 70 mm

Width 70 mm

Depth 50 mm

Connection

Conductor cross-section 2.50 - 2.50 mm²

Safety

Ingress Protection (IP) class IP20

Texts

Lighting Light colour cold white

Labelling Foils with imprint of symbols insertable

Imprint Without imprint

Suitable for

S.x/B.x

Sustainability

REACH-SVHC free Yes

RoHS conform Yes