

Product Datasheet

75642060



75642060



Touch sensor 2g thermostat, display, intg bus coupl. , KNX-R.1, glass p.white

Technical Features

Installation, mounting

Mounting on Flush mounting

Use conditions

Operating temperature -5 - 45 °C

Functions

With room temperature controller Yes

Power

Current consumption 23 mA

Dimensions

Built-in depth 12.90 mm

Built-in depth flush-mounted boxes 16 mm

Height 152 mm

Width 81 mm

Depth 23 mm

Equipment

Number of actuation points 4

Controls and indicators

With LED indication Yes

Materials

Colour Polar white

RAL code 9010

Material Glass

Surface finish Glossy

Accessories

Has labelling field No

Screen

With display Yes

Texts

Function For switch, push-button, dimmer, blind and thermostat functions
With valve protection function

Installation mode For vertical mounting

Operating mode Controller operating modes: comfort, standby, night and frost/heat
protection mode

Temperature Additional connection for external temperature sensor
Temperature measurement via internal Temperature sensor or external
communication object

Voltage Operation with non-choked output of KNX voltage supply possible (pay
attention to current consumption)
Separate auxiliary power supply needed

Sustainability

REACH-SVHC free Yes

RoHS conform Yes