


Product Datasheet

75642039



75642039



Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Functions

With room temperature controller	Yes
----------------------------------	-----

Power

Current consumption	23 mA
---------------------	-------

Dimensions

Built-in depth flush-mounted boxes	27 mm
Height	160 mm
Width	86 mm
Depth	5.70 mm

Equipment

Number of actuation points	4
----------------------------	---

Controls and indicators

With LED indication	Yes
---------------------	-----

Materials

Colour	Polar white
RAL code	9010
Material	Glass
Surface finish	Glossy

Accessories

Has labelling field	No
---------------------	----

Screen

With display	Yes
--------------	-----

Texts

Function	For switch, push-button, dimmer, blind and thermostat functions With valve protection function
Installation mode	For vertical mounting
Operating mode	Controller operating modes: comfort, standby, night and frost/heat protection mode
Temperature	Additional connection for external temperature sensor Temperature measurement via internal Temperature sensor or external communication object
Voltage	Operation with non-choked output of KNX voltage supply possible (pay attention to current consumption) Separate auxiliary power supply needed