



75642034



KNX glass sensor 2g thermostat, display,intg bus coupl.,KNX-TS sensor, al.

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Functions

With room temperature controller	Yes
----------------------------------	-----

Power

Current consumption	23 mA
---------------------	-------

Dimensions

Built-in depth	24.20 mm
Built-in depth flush-mounted boxes	27 mm
Height	160 mm
Width	86 mm
Depth	37.70 mm

Equipment

Number of actuation points	6
----------------------------	---

Controls and indicators

With LED indication	Yes
---------------------	-----

Materials

Colour	Aluminium
RAL code	9006
Material	Aluminium Glass
Surface finish	Glossy

Accessories

Has labelling field	No
---------------------	----

Screen

With display	Yes
--------------	-----

Texts

Function	For switch, push-button, dimmer, blind and thermostat functions With valve protection function
Installation mode	For vertical mounting
Operating mode	Controller operating modes: comfort, standby, night and frost/heat protection mode
Temperature	Additional connection for external temperature sensor Temperature measurement via internal Temperature sensor or external communication object
Voltage	Operation with non-choked output of KNX voltage supply possible (pay attention to current consumption) Separate auxiliary power supply needed

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes