




75642034



KNX glass sensor 2g thermostat, display,intg bus coupl.,KNX-TS sensor, al.

**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Use conditions**

Operating temperature -5 - 45 °C

**Functions**

With room temperature controller Yes

**Power**

Current consumption 23 mA

**Dimensions**

Built-in depth 24.20 mm  
 Built-in depth flush-mounted boxes 27 mm  
 Height 160 mm  
 Width 86 mm  
 Depth 37.70 mm

**Equipment**

Number of actuation points 6

**Controls and indicators**

With LED indication Yes

**Materials**

Colour Aluminium  
 RAL code 9006  
 Material Aluminium  
 Glass  
 Surface finish Glossy

**Accessories**

Has labelling field No

**Screen**

With display Yes

**Texts**

Function For switch, push-button, dimmer, blind and thermostat functions  
 With valve protection function  
 Installation mode For vertical mounting  
 Operating mode Controller operating modes: comfort, standby, night and frost/heat  
 protection mode  
 Temperature Additional connection for external temperature sensor  
 Temperature measurement via internal Temperature sensor or external  
 communication object  
 Voltage Operation with non-choked output of KNX voltage supply possible (pay  
 attention to current consumption)  
 Separate auxiliary power supply needed

**Sustainability**

REACH-SVHC free Yes  
 RoHS conform Yes