

Product Datasheet

16281909



16281909

Rocker, lab. field, lens, S.1/B.3/B.7, p. white, matt, plastic

Technical Features

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	54.90 mm
Width	55.70 mm
Depth	22 mm

Connectivity

Mounting type	Clamp mounting
---------------	----------------

Equipment

Monitoring window/light outlet	Yes
--------------------------------	-----

Accessories

Has labelling field	Yes
---------------------	-----

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

Texts

Imprint	Without imprint
Installation mode	Clamp fastening
Labelling	With labelling field
Lighting	For lighting and monitoring circuit
Push button	Also for KNX applications: push-button, 1-gang, and group push-button, 1-gang
Rocker switch/rocker push-button	For rocker push-buttons For change-over/intermediate switch

Suitable for

S.x/B.x	
---------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes