

Product Datasheet

JKD166TM



JKD166TM

125A Power/Lighting Board 6/6 Way Pan Assemblies Modbus Comms

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Architecture

Number of poles	3
-----------------	---

Functions

Has protection main switch	Yes
Overvoltage protection	No

Capacity

Number of modules	36
-------------------	----

Electric current

Rated current	125 A
---------------	-------

Dimensions

Depth	165.50 mm
Height	1100 mm
Width	465 mm
Thickness of sidewall	1 mm

Cover, door

Interlockable	No
Door/cover is transparent	Yes

Materials

RAL code	7035
Colour	Light grey
Material	Steel

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Connection

Number of accessible phases	3
-----------------------------	---

Scope of delivery

Number of RCCB in enclosure	0
-----------------------------	---

Equipment

With energy meter	Yes
Extension possible	Yes

Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP30