

# Product Datasheet

## FD72DN



FD72DN

Enclosure, NewVegaD, 1200x550x193mm, 168 modules, surface-mounted, distribution

Technical Features

Voltage

Nominal voltage230 - 400 V

Installation, mounting

Suitable for outdoor usageNo

Mounting onSurface mounting

Electric current

Rated current160 A

Equipment

Number of rails7

Number of rows7

With lockNo

Has neutral terminal blockNo

Capacity

Number of modules168

Dimensions

Height1200 mm

Width550 mm

Depth193 mm

Cover, door

Number of cabinet doors0

Number of locks0

Dimensions

Number of width units24

Cover, door

Door/cover is transparentNo

Connection

Number of conduit inlets4

Materials

MaterialMetal  
Plastic

RAL code9010

ColourPure white

Equipment

Has earthing terminal blockYes

Has mounting plateNo

Safety

Protection classIsolation class II

Impact resistance IKIK07

Ingress Protection (IP) classIP30

Locking typeWithout lock

Sustainability

RoHS conformYes