



FD72DN

Enclosure, NewVegaD, 1200x550x193mm, 168 modules, surface-mounted, distribution

**Technical Features**

**Voltage**

Nominal voltage 230 - 400 V

**Installation, mounting**

Suitable for outdoor usage No

Mounting on Surface mounting

**Electric current**

Rated current 160 A

**Equipment**

Number of rails 7

Number of rows 7

With lock No

Has neutral terminal block No

**Capacity**

Number of modules 168

**Dimensions**

Height 1200 mm

Width 550 mm

Depth 193 mm

**Cover, door**

Number of cabinet doors 0

Number of locks 0

**Dimensions**

Number of width units 24

**Cover, door**

Door/cover is transparent No

**Connection**

Number of conduit inlets 4

**Materials**

Material Metal  
Plastic

RAL code 9010

Colour Pure white

**Equipment**

Has earthing terminal block Yes

Has mounting plate No

**Safety**

Protection class Isolation class II

Impact resistance IK IK07

Ingress Protection (IP) class IP30

Locking type Without lock

**Sustainability**

RoHS conform Yes