



FD72GN

Enclosure, NewVegaD, 1200x550x193mm, 168 modules, surface-mounted, empty

**Technical Features**

**Dimensions**

|                       |         |
|-----------------------|---------|
| Height                | 1200 mm |
| Width                 | 550 mm  |
| Depth                 | 193 mm  |
| Thickness of sidewall | 1 mm    |

**Safety**

|                               |                    |
|-------------------------------|--------------------|
| Ingress Protection (IP) class | IP30               |
| Protection class              | Isolation class II |
| Locking type                  | Without lock       |
| Impact resistance IK          | IK07               |

**Equipment**

|                                 |   |
|---------------------------------|---|
| Number of flange plate openings | 2 |
|---------------------------------|---|

**Installation, mounting**

|                            |                  |
|----------------------------|------------------|
| Mounting on                | Surface mounting |
| Suitable for outdoor usage | No               |

**Materials**

|           |                  |
|-----------|------------------|
| Colour    | Pure white       |
| RAL code  | 9010             |
| Treatment | Powder coated    |
| Material  | Metal<br>Plastic |

**Equipment**

|                |   |
|----------------|---|
| Number of rows | 7 |
|----------------|---|

**Cover, door**

|                           |    |
|---------------------------|----|
| Number of cabinet doors   | 0  |
| Door/cover is transparent | No |

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 160 A |
|---------------|-------|

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|