



LNH0063M

**HRC LV fuse NH000 gG AC500V 63A double indicator with live gripping-lugs**

**Technical Features**

**Architecture**

Curve	gG
-------	----

**Fuse**

Fuse size	NH000
Fuse characteristics	gG

**Voltage**

Type voltage supply	AC/DC
Rated operational voltage Ue	500 - 500 V
Rated voltage at AC 50 Hz	500 - 500 V

**Electric current**

Rated current	63 A
---------------	------

**Use conditions**

Insulated	No
-----------	----

**Main electrical attributes**

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	120 kA
---	--------

**Power**

Total power loss under IN	5.40 W
---------------------------	--------

**Dimensions**

Height	58.50 mm
Width	21 mm
Depth	79 mm

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes