



WGCXS216EAKB

## 16A TWIN EURO-AMERICAN SOCKET, KB

### Technical Features

#### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

#### Electric current

|                |      |
|----------------|------|
| Output current | 0 mA |
| Rated current  | 16 A |

#### Voltage

|                |       |
|----------------|-------|
| Output voltage | 0-0 V |
|----------------|-------|

#### Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -20 - 45 °C |
|-----------------------|-------------|

#### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

#### Power

|                           |     |
|---------------------------|-----|
| Output power              | 0 W |
| Power consumption standby | 0 W |

#### Materials

|                                                        |                    |
|--------------------------------------------------------|--------------------|
| Colour                                                 | Knight black       |
| Surface finish                                         | Matt               |
| Material                                               | Polycarbonate (PC) |
| Treatment                                              | Coated             |
| Contains recycled material (% of total plastic weight) | 0 %                |

#### Dimensions

|        |       |
|--------|-------|
| Height | 30 mm |
| Width  | 86 mm |
| Depth  | 20 mm |

#### Cable

|              |     |
|--------------|-----|
| Cable length | 0 m |
|--------------|-----|

#### Dimensions

|                                    |       |
|------------------------------------|-------|
| Built-in depth flush-mounted boxes | 35 mm |
| Built-in depth                     | 20 mm |

#### Connection

|                                                          |                          |
|----------------------------------------------------------|--------------------------|
| Connector/plug type                                      | NEMA                     |
| Cross-section flexible conductor without wire end sleeve | 0.08 - 4 mm <sup>2</sup> |
| Number of conduit inlets                                 | 0                        |

#### Installation, mounting

|                               |                |
|-------------------------------|----------------|
| Mounting on                   | Flush mounting |
| Mounting-/Connection Position | Back           |

#### Connectivity

|                         |                |
|-------------------------|----------------|
| Type of connection      | Screw terminal |
| With claw mounting      | No             |
| Mounting type           | Screw mounting |
| Connector/plug type USB | NEMA           |

#### Equipment

|                                   |                  |
|-----------------------------------|------------------|
| Connector/plug type socket outlet | British Standard |
| Rotated central insert            | No               |
| With hinged lid                   | No               |
| With round protective earth pin   | No               |

|                                  |      |
|----------------------------------|------|
| <b>Equipment</b>                 |      |
| With signal lamp                 | No   |
| With lock                        | No   |
| <b>Accessories</b>               |      |
| Has labelling field              | No   |
| Pre-equipped with                | None |
| <b>Capacity</b>                  |      |
| Number of modules                | 0    |
| <b>Safety</b>                    |      |
| With enhanced contact protection | No   |
| Impact resistance IK             | IK02 |
| Ingress Protection (IP) class    | IP20 |
| <b>Functions</b>                 |      |
| With orientation lighting        | No   |
| With function lighting           | No   |
| <b>Identification</b>            |      |
| With imprint                     | No   |
| <b>Suitable for</b>              |      |
| shark                            |      |
| <b>Sustainability</b>            |      |
| Halogen free                     | Yes  |
| REACH-SVHC free                  | Yes  |
| RoHS conform                     | Yes  |