



HBD401H

Electronic earth leakage add-on block 4P 400A Idn adjustable, time delay

Technical Features

Electric current

Rated current	400 A
Rated residual operating current Idn	30 mA
	100 mA
	300 mA
	1000 mA
	3000 mA
	6000 mA

Architecture

Number of poles	4
-----------------	---

Safety

Residual current type	A
-----------------------	---

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6000 V