



JG220U

**IP66 40A 3P SW NEUTRAL UTILITY ISOLATOR**

**Technical Features**

**Architecture**

Number of poles	4
Type of pole	3P+N

**Electric current**

Rated current	40 A
Acceptable current rating AC21 category A	40 A
Acceptable current rating AC22 category A	40 A

**Voltage**

Rated operational voltage Ue	380 - 440 V
Rated insulation voltage Ui	440 V

**Installation, mounting**

Nominal tightening torque	2,50 - 2,50 Nm
---------------------------	----------------

**Dimensions**

Height	170 mm
Width	84 mm
Depth	87 mm

**Safety**

Ingress Protection (IP) class	IP66
-------------------------------	------

**Use conditions**

Operating temperature	-5 - 40 °C
-----------------------	------------

**Connection**

Cross-section rigid conductor	6 - 10 mm <sup>2</sup>
-------------------------------	------------------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Sustainability**

RoHS conform	Yes
--------------	-----