

# Product Datasheet

## VU60NE



VU60NE

Encl., Volta, flush, 5x12MOD, IP30, Version NCEE

### Technical Features

#### Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting

#### Electric current

Rated current	63 A
---------------	------

#### Power

Maximum power loss per cabinet at $\Delta T=20K$	27 W
--------------------------------------------------	------

#### Equipment

Number of rails	5
Number of rows	5
Number of section in width	1
With lock	No
Has neutral terminal block	No

#### Capacity

Number of modules	60
Number of half modules terminals per rail	120

#### Functions

With conduit inlets	Yes
---------------------	-----

#### Dimensions

Height	880.50 mm
Width	348 mm
Depth	94.50 mm
Built-in height	865 mm
Built-in width	335 mm

#### Cover, door

Number of cabinet doors	1
-------------------------	---

#### Dimensions

Built-in depth	90 mm
----------------	-------

#### Cover, door

Number of locks	0
-----------------	---

#### Dimensions

Number of width units	12
-----------------------	----

#### Cover, door

Door/cover is transparent	No
---------------------------	----

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Materials

Material	Plastic
RAL code	9010
Colour	Pure white

#### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Product Datasheet

VU60NE

Materials	
Ultraviolet-resistant	Yes
Safety	
Protection class	Isolation class II
Ingress Protection (IP) class	IP30
Locking type	Snap on lock Without lock
Glow wire test	650 °C
Sustainability	
RoHS conform	Yes