



ESC080

**Auxiliary contact 6A, 1NO+1NC**

**Technical Features**

**Electric current**

Rated current	6 A
---------------	-----

**Voltage**

Rated insulation voltage Ui	240 V
-----------------------------	-------

**Capacity**

Number of modules	0.50
-------------------	------

**Use conditions**

Operating temperature	-10 - 50 °C
Storage/transport temperature	-40 - 80 °C

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Connection**

Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1 - 6 mm <sup>2</sup>
Type of contacts	1NC+1NO

**Power**

Total power loss under IN	0.10 W
---------------------------	--------

**Dimensions**

Height	83 mm
Width	11 mm
Depth	60 mm

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes