



ESC080

Auxiliary contact 6A, 1NO+1NC

Technical Features

Electric current

Rated current	6 A
---------------	-----

Voltage

Rated insulation voltage Ui	240 V
-----------------------------	-------

Capacity

Number of modules	0.50
-------------------	------

Use conditions

Operating temperature	-10 - 50 °C
Storage/transport temperature	-40 - 80 °C

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Connection

Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1 - 6 mm ²
Type of contacts	1NC+1NO

Power

Total power loss under IN	0.10 W
---------------------------	--------

Dimensions

Height	83 mm
Width	11 mm
Depth	60 mm

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes