

# Product Datasheet

## ESC080



ESC080

### Auxiliary contact 6A, 1NO+1NC

#### Technical Features

##### Electric current

Rated current	6 A
---------------	-----

##### Voltage

Rated insulation voltage Ui	240 V
-----------------------------	-------

##### Capacity

Number of modules	0.50
-------------------	------

##### Use conditions

Operating temperature	-10 - 50 °C
Storage/transport temperature	-40 - 80 °C

##### Connectivity

Type of connection	Screw terminal
--------------------	----------------

##### Connection

Cross-section flexible conductor	1 - 6 mm²
Cross-section rigid conductor	1 - 6 mm²
Type of contacts	1NC+1NO

##### Power

Total power loss under IN	0.10 W
---------------------------	--------

##### Dimensions

Height	83 mm
Width	11 mm
Depth	60 mm

##### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes