



1001208300

**Cover plate toggle rotary switch/spring-return p-b, R.classic, glass, pol wh**

**Technical Features**

**Architecture**

Control/operation element	Toggle
---------------------------	--------

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Glass Thermoplastic
Treatment	Untreated

**Dimensions**

Height	81.40 mm
Width	81.40 mm
Depth	29 mm

**Connectivity**

Mounting type	Clamp mounting Screw connection
---------------	------------------------------------

**Equipment**

Monitoring window/light outlet	No
--------------------------------	----

**Accessories**

Has labelling field	No
---------------------	----

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

**Suitable for**

Serie R.classic	
-----------------	--

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes