



1001208300

Cover plate toggle rotary switch/spring-return p-b, R.classic, glass, pol wh

Technical Features

Architecture

Control/operation element	Toggle
---------------------------	--------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Glass Thermoplastic
Treatment	Untreated

Dimensions

Height	81.40 mm
Width	81.40 mm
Depth	29 mm

Connectivity

Mounting type	Clamp mounting Screw connection
---------------	------------------------------------

Equipment

Monitoring window/light outlet	No
--------------------------------	----

Accessories

Has labelling field	No
---------------------	----

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

Suitable for

Serie R.classic	
-----------------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes