



HBA125H

**Electronic earth leakage add-on block 3P 125A Idn adjustable, time delay**

**Technical Features**

**Electric current**

Rated current	125 A
Rated residual operating current Idn	30 mA
	100 mA
	300 mA
	1000 mA
	3000 mA
	6000 mA

**Architecture**

Number of poles	3
-----------------	---

**Safety**

Residual current type	A HI
-----------------------	------

**Voltage**

Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6000 V

**Connection**

Cross-section of input and output with screws, for massive conductors	2.5 - 95.0 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	2.5 - 70.0 mm <sup>2</sup>

**Sustainability**

RoHS conform	Yes
--------------	-----