



VB118W

Small distributor,vega,surface,1row,18M,IP40,QC-terminal,PE,transparent door

**Technical Features**

**Installation, mounting**

Mounting on Surface mounting

**Electric current**

Rated current 90 A

**Equipment**

Number of rails	1
Number of rows	1
With lock	No
Has neutral terminal block	No

**Capacity**

Number of modules 18

**Dimensions**

Height	325 mm
Width	400 mm
Depth	146 mm

**Cover, door**

Number of cabinet doors	1
Number of locks	1

**Dimensions**

Number of width units 18

**Cover, door**

Door/cover is transparent Yes

**Materials**

Material	Polystyrene (PS)
RAL code	9010
Colour	White

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

**Safety**

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock Without lock
Glow wire test	650 °C

**Sustainability**

RoHS conform Yes