

Product Datasheet

VB118J



VB118J

Small distributor,vega,surface,1row,18M,IP40,brass-terminal,PE,white door

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	90 A
---------------	------

Equipment

Number of rails	1
Number of rows	1
With lock	No
Has neutral terminal block	No

Capacity

Number of modules	18
-------------------	----

Dimensions

Height	325 mm
Width	400 mm
Depth	146 mm

Cover, door

Number of cabinet doors	1
Number of locks	1

Dimensions

Number of width units	18
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Polystyrene (PS)
RAL code	9010
Colour	White

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock Without lock
Glow wire test	650 °C

Sustainability

RoHS conform	Yes
--------------	-----