



VB118J

Small distributor,vega,surface,1row,18M,IP40,brass-terminal,PE,white door

**Technical Features**

**Installation, mounting**

Mounting on Surface mounting

**Electric current**

Rated current 90 A

**Equipment**

Number of rails 1

Number of rows 1

With lock No

Has neutral terminal block No

**Capacity**

Number of modules 18

**Dimensions**

Height 325 mm

Width 400 mm

Depth 146 mm

**Cover, door**

Number of cabinet doors 1

Number of locks 1

**Dimensions**

Number of width units 18

**Cover, door**

Door/cover is transparent No

**Materials**

Material Polystyrene (PS)

RAL code 9010

Colour White

**Equipment**

Has earthing terminal block Yes

Has mounting plate No

**Safety**

Impact resistance IK IK07

Ingress Protection (IP) class IP40

Locking type Snap on lock  
Without lock

Glow wire test 650 °C

**Sustainability**

RoHS conform Yes