



HCT201AR

**Load Break Switch Disconnecter h3+ P250 4P 200A FTC**

**Technical Features**

**Electric current**

Rated current	200 A
Rated short-time withstand current Icw IEC 60947	3.60 kA

**Architecture**

Number of poles	4
Control/operation element	Toggle

**Connection**

Cross-section rigid conductor	35 - 185 mm <sup>2</sup>
Cross-section flexible conductor	35 - 150 mm <sup>2</sup>

**Voltage**

Rated insulation voltage Ui	800 V
Rated impulse withstand voltage Uimp	8000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Functions**

Trip unit	Switch
-----------	--------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes