



VM11010

Consumer unit, Design30, dual row, 20+20way, 100A, switch-disconnector incomer

Technical Features

Installation, mounting

Mounting on Surface mounting

Architecture

Number of poles 2

Functions

Has protection main switch Yes

Overvoltage protection No

Installation, mounting

Suitable for outdoor usage No

Capacity

Number of modules 40

Electric current

Rated current 100 A

Dimensions

Depth 102.50 mm

Height 480 mm

Width 471 mm

Thickness of sidewall 1 mm

Cover, door

Interlockable No

Door/cover is transparent No

Materials

RAL code 9010

Colour Pure white

Material Steel

Connection

Number of accessible phases 1

Scope of delivery

Number of RCCB in enclosure 0

Equipment

Number of rows 2

Number of rails 2

Extension possible No

With socket outlet No

Safety

Impact resistance IK IK05

Ingress Protection (IP) class IP2XC

Number of earth leakage switches 300 mA 0

Sustainability

RoHS conform Yes