



HGR41EWC

**JK Multifunction Meter Pack 125A Pulsed and Modbus MID**

**Technical Features**

**Architecture**

Type of pole	3P+N
--------------	------

**Electric current**

Rated current	125 A
---------------	-------

**Capacity**

Number of modules	4
-------------------	---

**Dimensions**

Height	118.50 mm
Width	70 mm
Depth	66 mm

**Installation, mounting**

Mounting on	DIN rail Mounting plate
-------------	----------------------------

**Measurement**

Measuring system	Measurement transformer
Type of measuring instrument	Digital
Current measurement range	5 - 6000 A
Frequency measuring range	50 - 50 Hz

**Power supply**

Number of phases for power supply	3
-----------------------------------	---

**Functions**

Accuracy class	1
Tariff type	Multi-tariff
Is calibrated	Yes

**Use conditions**

Operating temperature	-10 - 55 °C
Storage/transport temperature	-20 - 75 °C

**Electric current**

Maximum measuring circuit current	6000 A
-----------------------------------	--------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Sustainability**

RoHS conform	Yes
--------------	-----