



961852505

Socket outlet w. earthing pin, screw term.s, Int. module inserts, anthr. matt

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 50 Hz

Materials

Colour	Anthracite
RAL code	7021
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	55.50 mm
Width	55.50 mm
Number of units	1
Built-in depth flush-mounted boxes	29 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection	Screw terminal
Mounting type	Built in installation Screw mounting

Equipment

Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	No
With round protective earth pin	Yes
With signal lamp	No
With lock	No

Accessories

Has labelling field No

Capacity

Number of modules 1

Safety

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint No

Texts

Cover	Central cover plate
Protection	Without enhanced contact protection
Type of connection	With screw terminals