



47526089



SCHUKO soc. out. hinged cover, enhanced contact prot., Q.x, p. white velvety

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white

RAL code 9010

Surface finish Velvety

Material Thermoplastic

Treatment Untreated

Dimensions

Height 71 mm

Width 71 mm

Number of units 1

Built-in depth flush-mounted boxes 35 mm

Built-in depth 32 mm

Connection

Connector/plug type Plug-in terminal

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Plug-in connection

Mounting type Screw mounting

Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid Yes

With round protective earth pin No

With signal lamp No

With lock No

Accessories

Has labelling field Yes

Cover, door

Type of lid Self-closing hinged cover

Capacity

Number of modules 1

Safety

With enhanced contact protection Yes

Impact resistance IK IK02

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Texts

Imprint	With imprint
Cover	Central cover plate
Type of connection	With plug-in terminals
Labelling	With labelling field

Suitable for

Q.x

Sustainability

Halogen free	Yes
RoHS conform	Yes