



WBSP2SUSB-MB

SIL. Twin Socket outlet + USB MB

Technical Features

Electric current

Rated current 10 A

Voltage

Output voltage 5 - 5 V

Frequency

Frequency 50 - 50 Hz

Materials

Colour Black

Surface finish Matt

Material Polycarbonate (PC)

Treatment Varnished

Dimensions

Height 77 mm

Width 117 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Mounting type Screw mounting

Connector/plug type USB AA

Equipment

Connector/plug type socket outlet Australian standard AS/NZS 3112

Rotated central insert No

With hinged lid No

Accessories

Has labelling field No

Capacity

Number of modules 2

Safety

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Identification

With imprint No

Texts

Fuse Short-circuit and overload-proof (electronic fuse)

Cover Full cover plate

Connectors jacks With 2 USB sockets type A

Sustainability

REACH-SVHC free Yes

RoHS conform Yes