



10238919

**Frame 3gang hor., lab. field, S.1, p. white glossy**

**Technical Features**

**Capacity**

|                   |   |
|-------------------|---|
| Number of gangs   | 3 |
| Number of modules | 3 |

**Materials**

|                |             |
|----------------|-------------|
| Colour         | Polar white |
| RAL code       | 9010        |
| Surface finish | Glossy      |
| Material       | Duroplastic |
| Treatment      | Untreated   |

**Dimensions**

|        |          |
|--------|----------|
| Height | 80.50 mm |
| Width  | 223 mm   |
| Depth  | 9.50 mm  |

**Accessories**

|                     |     |
|---------------------|-----|
| Has labelling field | Yes |
|---------------------|-----|

**Installation, mounting**

|                               |            |
|-------------------------------|------------|
| Mounting-/Connection Position | Horizontal |
|-------------------------------|------------|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
| Impact resistance IK          | IK02 |

**Texts**

|                   |                      |
|-------------------|----------------------|
| Installation mode | Clamp fastening      |
| Labelling         | With labelling field |

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |