



JAC312

Enclosed Switch Disconnecter TPN 125A

Technical Features

Electric current

Rated current	125 A
Rated short-time withstand current I _{cw} 1s IEC 60947	7 kA

Use conditions

Operating temperature	-5 - +40 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated insulation voltage U _i	800 V
Rated impulse withstand voltage U _{imp}	8 kV

Safety

Ingress Protection (IP) class	IP41
-------------------------------	------

Dimensions

Width	250 mm
Depth	150 mm

Installation, mounting

Mounting on	Wall mounting
-------------	---------------