



936552518

Series switch, common input terminal, Integro - Design Flow/Pure, chr gl, galv

**Technical Features**

**Electric current**

Switching current 10 A

**Voltage**

Rated voltage 250 V

**Materials**

Colour Chrome  
RAL code 9006  
Surface finish Glossy  
Material Thermoplastic  
Treatment Chrome plated  
Coated

**Identification**

Assembly arrangement Basic element with central cover plate

**Connectivity**

Mounting type Built in installation  
Screw mounting

**Controls and indicators**

Number of buttons 2

**Dimensions**

Dimensions 55.50 x 55.50 mm  
Built-in depth 10 mm  
Built-in depth flush-mounted boxes 13 mm

**Safety**

Ingress Protection (IP) class IP20

**Architecture**

Control/operation element Double rocker

**Electric current**

Rated current 10 A

**Texts**

Installation mode For screw fastening  
Type of connection With screw terminals  
Lighting Without lighting (cannot be illuminated)  
Switch mode Series

**Sustainability**

RoHS conform Yes