



170108

Technical Features

Detection

Detection angle	360 - 360
Type of sensor	Presence detector

Lighting

Response brightness adjustable	10 - 1000 lx
--------------------------------	--------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Recommended installation height	2.5 - 3.5 m
---------------------------------	-------------

Use conditions

Operating temperature	5 - 35 °C
-----------------------	-----------

Materials

Colour	Polar white
Material	Thermoplastic

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Texts

Function	With communication between individual units connected in parallel (controller system formation)
Installation mode	For ceiling mounting (also on a 60 wall box)
Type of connection	With plug-in terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes