



47903512



Combi.switch/SCHUKO soc.out. hinged cover surf.-mtd,enhncd contact prot.,W1

Technical Features

Dimensions

Dimensions	147 x 76 mm
Built-in depth flush-mounted boxes	0 mm

Electric current

Rated current	16 A
Switching current	10 A

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	White
RAL code	7011 9010
Material	Thermoplastic
Surface finish	Matt

Safety

Ingress Protection (IP) class	IP55
With enhanced contact protection	No

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Equipment

With signal lamp	No
Connector/plug type socket outlet	SCHUKO
Rotated central insert	No

Accessories

Has labelling field	No
---------------------	----

Texts

Installation mode	For vertical mounting
Protection	Without enhanced contact protection
Sealing	With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside
Type of connection	With plug-in terminals

Sustainability

Halogen free	Yes
RoHS conform	Yes