



125A TPN board, invicta, 4 + 4 way, with wiring, surface mounting

Technical Features

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Electric current

| | |
|---|------|
| Breaking and opening capacity I _{dm} | 0 kA |
|---|------|

Equipment

| | |
|------------------------|---------------|
| Has mounting plate | No |
| Equipped with switch | No switch |
| Number of switches | 0 |
| Type of busbar chassis | Split chassis |

Capacity

| | |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

Dimensions

| | |
|--------|--------|
| Height | 665 mm |
| Width | 445 mm |
| Depth | 125 mm |

Cover, door

| | |
|---------------------------|----|
| Number of cabinet doors | 1 |
| Door/cover is transparent | No |

Materials

| | |
|----------|------------|
| Material | Steel |
| RAL code | 9002 |
| Colour | Grey white |

Safety

| | |
|-------------------------------|------------------------------|
| Protection class | Isolation class I |
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP41 |
| Locking type | Special tool Without lock |

Architecture

| | |
|-----------------|----|
| Number of poles | 12 |
|-----------------|----|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|