



3862

**Rotary switch 2pole off, light control**

**Technical Features**

**Electric current**

Switching current 20 A

**Installation, mounting**

Mounting on Flush mounting

**Voltage**

Rated voltage 250 V

**Materials**

Material Metal  
Plastic

Treatment Untreated

**Identification**

Assembly arrangement Basic element

**Connectivity**

Mounting type Screw mounting

**Dimensions**

Dimensions 71 x 71 mm

Built-in depth 31 mm

Built-in depth flush-mounted boxes 35 mm

**Safety**

Ingress Protection (IP) class IP20

**Electric current**

Rated current 20 A

**Texts**

Installation mode Without spreader claws

Type of connection With screw terminals

Switch mode 2-pole off

**Sustainability**

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes