



170110

Technical Features

Dimensions

| | |
|---------------------|---------------|
| Installation height | 2.50 - 2.50 m |
| Assembling height | 42 mm |

Detection

| | |
|-----------------------------|-------------------|
| Type of sensor | Presence detector |
| Detection diameter on floor | 8 - 8 m |
| Detection angle | 360 - 360 ° |
| Detection angle adjustable | 360 - 360 ° |

Materials

| | |
|----------------|---------------|
| Colour | Polar white |
| Surface finish | Matt |
| Treatment | Untreated |
| Material | Thermoplastic |

Reach distance

| | |
|-----------------------------------|-----|
| Max. transmission range frontally | 8 m |
| Max. transmission range sideways | 4 m |

Lighting

| | |
|--------------------------------|--------------|
| Response brightness adjustable | 10 - 1000 lx |
|--------------------------------|--------------|

Settings

| | |
|--------------------------------|-----|
| Response brightness adjustable | Yes |
|--------------------------------|-----|

Use conditions

| | |
|-----------------------|-----------|
| Operating temperature | 5 - 35 °C |
|-----------------------|-----------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Texts

| | |
|----------|---|
| Function | With diaslide-presentation function With dimming function (soft-off) when using BLC dimmer inserts |
|----------|---|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |