



WGML111E

10A 1G press switch mark "exit"

**Technical Features**

**Electric current**

Switching current	10 A
-------------------	------

**Voltage**

Rated voltage	250 V
---------------	-------

**Architecture**

Control/operation element	Single rocker
---------------------------	---------------

**Materials**

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated
Transparent	No

**Dimensions**

Height	86 mm
Width	86 mm
Depth	25 mm
Built-in depth flush-mounted boxes	35 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Controls and indicators**

Number of buttons	1
With feedback signal contact	No

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Accessories**

Has labelling field	No
---------------------	----

**Texts**

Imprint	With imprint " " and symbol key
---------	---------------------------------

**Suitable for**

shark	
-------	--

**Sustainability**

RoHS conform	Yes
--------------	-----