



WMMTVFB



Single IEC Female Euromodule Black

Technical Features

Connectivity

Mounting type	Snap-on mounting
---------------	------------------

Attenuation

Tap loss at 860 MHz	0.30 dB
---------------------	---------

Connection

Connector/plug type	Direct socket
---------------------	---------------

Frequency

Frequency bandwidth	5 - 860 MHz
---------------------	-------------

Equipment

Number of outputs	1
-------------------	---

Materials

Material	Urea formaldehyde
Colour	White

Dimensions

Depth	24 mm
-------	-------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes