



11357204

**Centre plate f. speed cont., setting knob, K.5, stainl. steel, metal matt finish**

**Technical Features**

**Architecture**

Control/operation element	Rotative
---------------------------	----------

**Materials**

Colour	Stainless steel
RAL code	9022
Surface finish	Matt
Material	Metal Stainless steel
Treatment	Untreated

**Dimensions**

Height	55 mm
Width	71 mm
Depth	20 mm
Diameter axis	4 mm

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Equipment**

Monitoring window/light outlet	No
--------------------------------	----

**Accessories**

Has labelling field	No
---------------------	----

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

**Texts**

Imprint	With imprinted symbol curve
Installation mode	For screw fastening

**Suitable for**

K.x	
-----	--

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes