



11357204

Centre plate f. speed cont., setting knob, K.5, stainl. steel, metal matt finish

Technical Features

Architecture

Control/operation element	Rotative
---------------------------	----------

Materials

Colour	Stainless steel
RAL code	9022
Surface finish	Matt
Material	Metal Stainless steel
Treatment	Untreated

Dimensions

Height	55 mm
Width	71 mm
Depth	20 mm
Diameter axis	4 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Equipment

Monitoring window/light outlet	No
--------------------------------	----

Accessories

Has labelling field	No
---------------------	----

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

Texts

Imprint	With imprinted symbol curve
Installation mode	For screw fastening

Suitable for

K.x	
-----	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes