



SM151

**Digital ammeter 0-150A indirect reading**

**Technical Features**

**Capacity**

Number of modules	4
-------------------	---

**Measurement**

Current measurement range	0 - 150 A
---------------------------	-----------

**Use conditions**

Operating temperature	-10 - 55 °C
Storage/transport temperature	-40 - 70 °C

**Connection**

Cross-section flexible conductor	6 mm <sup>2</sup>
Cross-section rigid conductor	10 mm <sup>2</sup>

**Dimensions**

Height	85 mm
Width	70 mm
Depth	54 mm

**Measurement**

Type of measuring instrument	Digital
------------------------------	---------

**Power**

Power consumption VA	1 VA
----------------------	------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Installation, mounting**

Mounting on	DIN rail
-------------	----------

**Functions**

Accuracy class	0.01
----------------	------

**Frequency**

Frequency	45 - 65 Hz
-----------	------------

**Power**

Total power loss under IN	1 W
---------------------------	-----

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes