



WGCXT1RJAS

**RJ11 outlet (1mod);as**

**Technical Features**

**Frequency**

Transmission bandwidth	0-100 MHz
------------------------	-----------

**Equipment**

With transparent label holder	No
-------------------------------	----

Number of outputs	1
-------------------	---

**Use conditions**

Operating temperature	-20 - 45 °C
-----------------------	-------------

**Equipment**

With hinged lid	No
-----------------	----

**Materials**

Colour	Aurora silver
--------	---------------

**Connection**

Connector/plug type	RJ45
---------------------	------

**Materials**

Material	Polycarbonate (PC)
----------	--------------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Voltage**

Rated voltage	0 V
---------------	-----

**Electric current**

Rated current	0 A
---------------	-----

**Dimensions**

Built-in depth	27 mm
----------------	-------

**Sustainability**

RoHS conform	Yes
--------------	-----