



20316086



Temp. cont.,NCcontact,Cen. plate,24V AC/DC,rocker switch,Q.1/Q.3,ant.velv.lacq.

**Technical Features**

**Architecture**

Control/operation element Rotative

**Electric current**

Rated current 4 A  
Max. switching current 10 A

**Voltage**

Nominal voltage 24 - 24 V

**Power supply**

Supply voltage 24 V AC/DC

**Frequency**

Frequency 50 - 60 Hz

**Settings**

Comfort temperature setpoint 5 - 30 °C

**Materials**

Colour Anthracite  
RAL code 7016  
Surface finish Velvety  
Material Metal Plastic

**Dimensions**

Height 71 mm  
Width 71 mm  
Depth 50.90 mm

**Screen**

With display No

**Equipment**

Switching temperature difference 0.50 K  
Type of thermostat Room thermostat  
Type of probe Bimetal

**Safety**

Ingress Protection (IP) class IP20

**Connection**

Type of contacts 1NC

**Compatibility**

Type of HVAC control Heating

**Use conditions**

Energy efficiency class I (1%)

**Texts**

Installation mode Without spreader claws  
Type of connection With plug-in terminals  
Thermal re-circulation With thermal return  
Imprint With imprint  
Junction With separate connection for night lowering

**Sustainability**

REACH-SVHC free Yes  
RoHS conform Yes