



KCN325

Distribution between 3 rows in consumer unit, 125 mm, for RCCB

Technical Features

Electric current

Rated current 63 A

Architecture

Number of poles 2

Dimensions

Length 271 mm

Voltage

Rated impulse withstand voltage Uimp 4000 V

Connection

Cross-section rigid conductor 16 mm²

Sustainability

REACH-SVHC free Yes

RoHS conform Yes